

# LOW TEMPERATURE WASHING MONITOR <sup>+</sup>

For Assessing the Efficiency of Washing Processes up to 40 °C


This test fabric is soiled with a mixture of fatty components, pigments and protein. It is useable at low washing temperatures.

**article 123**  
soiling on cotton




Washparameters in accordance to IEC 60456


## General washing behaviour on HA/VA machines (ECE'98/IEC-A\*)



## Comparison with article 106/118 on VA machine (IEC-A\*)



## Comparison with article 106/118 on HA machine (IEC-A\*)



Article 123 is sensitive to the washing temperature, to protease and to detergents. On request, the monitor is also available on a polyester/cotton fabric, showing a similary performance.